




Wiremold  
WMFB1KS4B Series Single-Gang Floor Box Assembly  
Part No. WMFB1KS4B



Includes single-gang box, 106 adapter with four openings for communication devices, and brass cover with two screw plugs. For hole cut dimensions, see installation instructions sheet. Box Dimensions: 2 1/8" W x 3 3/4" L x 3 7/8" D (54mm W x 95mm L x 98mm D) Device Plate: 3 1/8" W x 4 15/16" L (79mm W x 125mm L).

## Features & Benefits

Includes single-gang box, 106 adapter with four openings for communication devices, and brass cover with two screw plugs. Box Dimensions: 2 1/8" W x 3 3/4" L x 3 7/8" D (54mm W x 95mm L x 98mm D) Device Plate: 3 1/8" W x 4 15/16" L (79mm W x 125mm L).

For hole cut dimensions, see installation instructions sheet.

## Specifications

### General Info

|                   |   |                    |  |
|-------------------|---|--------------------|--|
| Product Line      | Wiremold  | UPC Number         | 786564053989   |
| Country Of Origin | Mexico  | Material           | PVC  |
| Construction      | Not Assembled   | Cover Style        | Surface  |
| Cover Material    | Brass   | Application Sector | Commercial, Residential                              |
| Standard          | cULus Listed Nonmetallic Outlet Boxes: File E143222 Guide QCMZ. Meets Article 314.27(C) of NEC. | Warranty Type      | 1-Year from Installation or 2-Years from Day of Sale |
| Type              | Floor Box   |                    |  |

### Dimensions

|                  |          |                   |         |
|------------------|----------|-------------------|---------|
| Product Width US | 2.125 in | Product Weight US | 1.04 lb |
|------------------|----------|-------------------|---------|

---

|                  |          |               |                |
|------------------|----------|---------------|----------------|
| Product Depth US | 3.875 in | Knockout Size | 1/2 in, 3/4 in |
|------------------|----------|---------------|----------------|

---

### Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

### Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

### Technical Information

---

|            |      |                  |        |
|------------|------|------------------|--------|
| Floor Type | Wood | Service Capacity | Single |
|------------|------|------------------|--------|

---

|                     |      |              |        |
|---------------------|------|--------------|--------|
| Minimum Floor Depth | 5 in | Box Capacity | 1 Gang |
|---------------------|------|--------------|--------|

---

|             |               |          |          |
|-------------|---------------|----------|----------|
| Cable Entry | Through Floor | Box Type | Recessed |
|-------------|---------------|----------|----------|

---

|                            |         |
|----------------------------|---------|
| Depth Behind Device Plates | 3.87 in |
|----------------------------|---------|

---