



**Wiremold  
Outdoor Ground Box**  
Part No. XB814



The single service 2-gang Outdoor Ground Box is made from a UV rated nonmetallic material and has been designed to withstand the harsh outdoor environments. The box can accept up to (2) 1 1/4" trade size PVC conduit feeds. Boxes are designed to be installed separately or ganged together, for greater capacity and flexibility. They work with XB814 cover assemblies (sold separately).

## Features & Benefits

cUL Coming Soon

UL listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use – Tested and listed by Underwriters Laboratories, Inc. to UL2996 and UL50E for use in the ground in all weather conditions.

Outdoor-Rated Construction – UV and chemical-resistant F1 rated nonmetallic materials, allows the box to hold up for years to come.

Modular design – Boxes are designed to interlock allowing endless number of boxes in the same location. Provides service separation, everything in one location, and easier installation.

Air Pocket Design – This innovative design traps and maintains an air pocket protecting the devices, plugs and connections from water, snow, and ice. Allow for safer operation year round.

ADA Compliant – Meets all specifications for ADA guidelines.

Holds up to 5000 lbs – Has an ANSI/SCTE 77 Tier 5 rating and can hold up to 5,000 lbs of load allowing for the occasional tractor or non-deliberate vehicular traffic.

Flush to the Finished Ground – Designed to be flush with any surface, grass, dirt, walkways, patios, etc.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776187182
Country Of Origin	China	Material	Plastic
Conduit Size	3/4 - 1-1/4 in	Construction	Assembled

---

Features	ADA Compliant	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit
----------	---------------	--------------------	---

---

Standard	UL Listed Outdoor In-Ground Boxes: File E486738 Guide QCNL.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
----------	---	---------------	--

---

Type	Ground Box
------	------------

---

### Dimensions

---

Product Width US	8.125 in	Product Weight US	9.4 lb
Product Height US	10.75 in	Product Length US	16.125 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E486738	cULus Listed	Yes
---------------------	---------	--------------	-----

---

### Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

### Technical Information

---

Service Capacity	Single	Enclosure Type	Type 6P
Load Capacity	5000 lb		

---