



Wiremold
800LCK Series Steel Floor Box
Part No. 800LCK



This semi-adjustable stamped steel floor box provides an excellent and economical activation solution for the low density power or communication requirements in above grade open space areas. These boxes feature an aesthetic, low profile brass appearance that allows you to activate your wiring without obstructions. These boxes also accept the 525 Series Service Fittings, allowing for more configuration options and a die-cast aluminum look. Typical applications would be in any large open space area.

Features & Benefits

Stamped steel construction. Meets requirements for above grade applications. Lower cost alternative to cast iron boxes on above grade applications.

Activation flush or pedestal. Flexibility to meet power or data wiring requirements. Variety of aesthetically pleasing cover options.

Single power receptacles available. An inexpensive option for low density power requirements for open space areas.

Covers are interchangeable for cast iron and stamped steel. More activations to meet any decor.

Specifications

General Info

| | | | |
|-------------------|---|--------------------|--|
| Product Line | Wiremold | UPC Number | 786564260363 |
| Country Of Origin | Mexico | Material | Steel |
| Construction | Assembled | Cover Style | Flush |
| Cover Material | Brass | Application Sector | Commercial |
| Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |
| Type | Floor Box | | |

Dimensions

| | | | |
|-------------------|---------|-------------------|--------|
| Product Weight US | 1.61 lb | Product Height US | 3.0 in |
|-------------------|---------|-------------------|--------|

| | | | |
|-------------------|----------|----------------|----------------------|
| Product Length US | 4.187 in | Cubic Capacity | 23.6 in ³ |
|-------------------|----------|----------------|----------------------|

| | |
|---------------|----------------|
| Knockout Size | 1/2 in, 3/4 in |
|---------------|----------------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|------------|------------------------|------------------|--------|
| Floor Type | Carpet, Concrete, Tile | Service Capacity | Single |
|------------|------------------------|------------------|--------|

| | | | |
|--------------|--------|-------------|----------|
| Box Capacity | 1 Gang | Cable Entry | Knockout |
|--------------|--------|-------------|----------|

| | | | |
|----------|-------------|----------------------------|--------|
| Box Type | Above-Grade | Depth Behind Device Plates | 2.6 in |
|----------|-------------|----------------------------|--------|
