



The AF1 Raised Floor and Stage Floor Box provides three separate compartments that accommodate a combination of power, communication and audio/video devices. This combination is accomplished with the built-in service dividers. These dividers are arranged in a single-double, single-gang configuration. Die-cast aluminum housing provides added strength and reliability.

Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as color choice of black, brown, or gray. NOTE: AF1 Floor Boxes are available in a prewired (power only) version. Consult factory for ordering information. For information on prewired versions with Walkerflex, see the Walkerflex Pages of this website. All boxes and plates are sold separately.

## Features & Benefits

The AF1 Raised Floor and Stage Floor Box provides three separate compartments that accommodate a combination of power, communication and audio/video devices. This combination is accomplished with the built-in service dividers.

These dividers are arranged in a single-double, single-gang configuration. Die-cast aluminum housing provides added strength and reliability.

Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as color choice of black, brown, or gray.

NOTE: AF1 Floor Boxes are available in a prewired (power only) version. Consult factory for ordering information. For information on prewired versions with Walkerflex, see the Walkerflex Pages of this website. All boxes and plates are sold separately.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786564519287
Country Of Origin	United States	Material	Die-Cast Aluminum
Construction	Assembled	Cover Material	Polycarbonate
Application Sector	Commercial	Standard	UL Listed Classified Raised Floor Box: File E2961 Guide QCIT, UL Listed Classified Raised Floor Box (prewired): File E51105 Guide QQVX, Meets Article 314 of NEC. Meets Article 12 2500 of CEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box

---

## Dimensions

---

Product Weight US	5.0 lb	Cubic Capacity	208.6 in <sup>3</sup>
Knockout Size	1/2 in, 3/4 in		

---

## **Listing Agencies / 3rd Party Agencies**

---

cULus Listing Number	E2961	cULus Listed	Yes
----------------------	-------	--------------	-----

---

## Trade Programs

---

USMCA	Yes
-------	-----

---

## Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Floor Type	Carpet, Raised, Tile	Service Capacity	Triple
------------	----------------------	------------------	--------

---

Minimum Floor Depth	5 in	Box Capacity	4 Gangs
---------------------	------	--------------	---------

---

Cable Entry	Through Floor	Box Type	Recessed
-------------	---------------	----------	----------

---

Depth Behind Device Plates	2.75 in
----------------------------	---------

---