

Han-Snap Latching parts w. strain relief



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 33 000 9991 |
| Specification | Han-Snap Latching parts w. strain relief |
| HARTING eCatalogue | https://harting.com/09330009991 |

Identification

| | |
|------------------------------|--------------------|
| Category | Accessories |
| Series | Han-Snap® |
| Type of accessory | Latching parts |
| Description of the accessory | With strain relief |

Version

| | |
|---------------|---|
| Pack contents | 1 latching part with strain relief 1 latching part |
|---------------|---|

Technical characteristics

| | |
|--|---|
| Tightening torque | 0.8 Nm |
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP20 |
| Retention force | 200 N Without guiding 300 N With guiding |

Material properties

| | |
|---|--|
| Material (accessories) | Polycarbonate (PC) |
| Colour (accessories) | RAL 7032 (pebble grey) |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |

Material properties

| | |
|--------------------------------------|---|
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead |
| ECHA SCIP number | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) R23 (HL 1-3) |

Specifications and approvals

| | |
|----------------|--|
| Specifications | IEC 60068-2-6 Vibration (sinusoidal) IEC 60068-2-27 Shock |
|----------------|--|

Commercial data

| | |
|--------------------------------|----------------------------------|
| Packaging size | 10 |
| Net weight | 19.5 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| GTIN | 5713140050686 |
| eCl@ss | 27440392 Connector (accessories) |
| ETIM | EC002939 |
| UNSPSC 24.0 | 39121400 |