

## Han3M RJ45 GL Cat6A plug 8p met.



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 115 1522
Specification	Han3M RJ45 GL Cat6A plug 8p met.
HARTING eCatalogue	<a href="https://harting.com/09451151522">https://harting.com/09451151522</a>

### Identification

Category	Connectors
Series	RJ45
Series of hoods/housings	Han A®
Element	Cable connector
Type of hood/housing	Hood
Description of hood/housing	Straight

### Version

Termination method	Piercing termination
Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Pack contents	Connector insert Hoods / Housings Cable gland Assembly instructions

### Technical characteristics

Conductor cross-section	0.08 ... 0.22 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 28 ... AWG 24 Stranded
Wire outer diameter	≤1.05 mm
Transmission characteristics	Cat. 6 Class E up to 250 MHz

## Technical characteristics

	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Data rate	
Limiting temperature	-40 ... +70 °C
Storage temperature	+5 ... +50 °C
Degree of protection acc. to IEC 60529	IP65
	IP67
Cable diameter	5 ... 9 mm

## Material properties

Material (hood/housing)	Zinc die-cast
Colour (hood/housing)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL

## Commercial data

Packaging size	10
----------------	----

## Commercial data

Net weight	125.72 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140058828
eCl@ss	27440113 Rectangular connectors (set)
ETIM	EC002636
UNSPSC 24.0	39121408