

## 7/8 Cable Assembly 4p+PE an/- f/- 10,0m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 34 990 0598 100                                                                  |
| Specification      | 7/8 Cable Assembly 4p+PE an/- f/- 10,0m                                             |
| HARTING eCatalogue | <a href="https://harting.com/21349900598100">https://harting.com/21349900598100</a> |

### Identification

|               |                           |
|---------------|---------------------------|
| Category      | System cabling            |
| Series        | Circular connectors 7/8"  |
| Element       | Cable assemblies          |
| Specification | Pre-assembled on one side |
| Connector 1   | 7/8"<br>Female Angled     |
| Type of cable | Copper cable (round)      |

### Version

|                                   |                              |
|-----------------------------------|------------------------------|
| Cable length                      | 10 m                         |
| Number of cores                   | 5                            |
| Core structure                    | 5x 1.5 mm <sup>2</sup><br>PE |
| Number of contacts                | 5                            |
| Number of power contacts          | 4                            |
| Number of special contacts        | 1                            |
| Specification of special contacts | PE contact                   |

### Material properties

|                  |                                                        |
|------------------|--------------------------------------------------------|
| Material (cable) | PUR (polyurethane)                                     |
| Colour (cable)   | Black                                                  |
| RoHS             | compliant with exemption                               |
| RoHS exemptions  | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status       | compliant with exemption                               |



**Pushing Performance**  
 Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| China RoHS                           | 50                                   |
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | 0d7d3693-d625-47ab-934a-d241bf72c86e |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead<br>Nickel                       |

## Specifications and approvals

|           |    |
|-----------|----|
| Approvals | CE |
|-----------|----|

## Commercial data

|                                |                                              |
|--------------------------------|----------------------------------------------|
| Packaging size                 | 1                                            |
| Net weight                     | 1,156 g                                      |
| Country of origin              | Czechia                                      |
| European customs tariff number | 85444290                                     |
| GTIN                           | 5713140146990                                |
| eCl@ss                         | 27060390 Ready-made data cable (unspecified) |
| ETIM                           | EC002599                                     |
| UNSPSC 24.0                    | 26121600                                     |