

PMST (9X38) OG - Insert label



0830966

<https://www.phoenixcontact.com/us/products/0830966>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, orange, unmarked, mounting type: latching, Number of individual labels: 1



Your advantages

- The medium marking label is used in conjunction with insertable UCT-PMP ... labels in the CARRIER-PMP
- They are used to clearly identify devices and control cabinets
- They are secured in the CARRIER-PMP using rivets

Commercial data

Item number	0830966
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	BG261Z
GTIN	4046356912402
Weight per piece (including packing)	0.53 g
Weight per piece (excluding packing)	0.47 g
Country of origin	DE

PMST (9X38) OG - Insert label



0830966

<https://www.phoenixcontact.com/us/products/0830966>

Technical data

Product properties

Product type	Plant marker
Area of application	Identification of flow substances according to DIN 2403

Marking

Number of individual labels	1
Number of individual labels per row	1

Dimensions

Width	9 mm
Length	38 mm

Material specifications

Color	orange (RAL 2003)
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	10 °C ... 30 °C
Recommended humidity (storage/transport)	40 % ... 70 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	12 months

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

PMST (9X38) OG - Insert label



0830966

<https://www.phoenixcontact.com/us/products/0830966>

Classifications

ECLASS

ECLASS-13.0	27281104
-------------	----------

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

PMST (9X38) OG - Insert label



0830966
<https://www.phoenixcontact.com/us/products/0830966>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com