

CRIMPFOX-C120 RCT 70-1/DIE - Crimp insert



1212319

<https://www.phoenixcontact.com/us/products/1212319>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die (pair), for CRIMPFOX-C120, for copper tube lug 10 + 70 mm², WM crimp

Commercial data

Item number	1212319
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356454650
Weight per piece (including packing)	135.8 g
Weight per piece (excluding packing)	135.8 g
Customs tariff number	82079091
Country of origin	DE

CRIMPFOX-C120 RCT 70-1/DIE - Crimp insert



1212319

<https://www.phoenixcontact.com/us/products/1212319>

Technical data

Product properties

Product type	Die
Compression	HEX crimp
Product property	Replacement insert for CRIMPFOX-C120 crimping pliers
Min. cross section	10 mm ²
Max. cross section	70 mm ²
AWG min	7
AWG max	2/0

Connection data

Conductor connection

Cross section range, metric	10 mm ² ... 70 mm ²
-----------------------------	---

Material specifications

Color	black
-------	-------

CRIMPFOX-C120 RCT 70-1/DIE - Crimp insert



1212319

<https://www.phoenixcontact.com/us/products/1212319>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212319>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-C120 RCT 70-1/DIE - Crimp insert



1212319

<https://www.phoenixcontact.com/us/products/1212319>

Classifications

ECLASS

ECLASS-15.0	21043892
ECLASS-13.0	21043892

ETIM

ETIM 9.0	EC011822
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-C120 RCT 70-1/DIE - Crimp insert



1212319

<https://www.phoenixcontact.com/us/products/1212319>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com