

1212331  
<https://www.phoenixcontact.com/us/products/1212331>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die (upper part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 6 ... 70 mm<sup>2</sup>, indent crimp

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212331       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH313Z        |
| GTIN                                 | 4046356454773 |
| Weight per piece (including packing) | 88.8 g        |
| Weight per piece (excluding packing) | 88.8 g        |
| Customs tariff number                | 82079091      |
| Country of origin                    | DE            |

# CRIMPFOX-C120 RC 70/M-DIE - Crimp insert



1212331

<https://www.phoenixcontact.com/us/products/1212331>

## Technical data

### Product properties

|                  |                                                      |
|------------------|------------------------------------------------------|
| Product type     | Die                                                  |
| Compression      | Indent crimp                                         |
| Product property | Replacement insert for CRIMPFOX-C120 crimping pliers |

### Connection data

#### Conductor connection

|                             |                                          |
|-----------------------------|------------------------------------------|
| Cross section range, metric | 6 mm <sup>2</sup> ... 70 mm <sup>2</sup> |
|-----------------------------|------------------------------------------|

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX-C120 RC 70/M-DIE - Crimp insert



1212331

<https://www.phoenixcontact.com/us/products/1212331>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212331>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-C120 RC 70/M-DIE - Crimp insert



1212331

<https://www.phoenixcontact.com/us/products/1212331>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043892 |
| ECLASS-15.0 | 21043892 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC011822 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-C120 RC 70/M-DIE - Crimp insert



1212331  
<https://www.phoenixcontact.com/us/products/1212331>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)