

SS-3R 20X7 WH - Contactor marker

0807740

<https://www.phoenixcontact.com/us/products/0807740>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker sheet, for Siemens SIRIUS 3R switchgear series, 40-section, 20 strips à 2 markers, labeling with M-PEN, CMS system or BMKT labels, lettering field: 20 x 7 mm

Commercial data

Item number	0807740
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG20
Product key	BG2413
GTIN	4017918156954
Weight per piece (including packing)	12.4 g
Weight per piece (excluding packing)	9.7 g
Customs tariff number	39269097
Country of origin	DE

SS-3R 20X7 WH - Contactor marker

0807740

<https://www.phoenixcontact.com/us/products/0807740>



Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Gerätemarker
Pitch	20 mm

Marking

Number of individual labels	40
Number of individual labels per row	2
Number of marker strips	20

Dimensions

Width	19.00 mm
Height	7.50 mm
Depth	1.00 mm
Pitch	20 mm

Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V0
Base element material	ABS

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN 30646
	DIN VDE 0611-1

Mounting

Mounting type	latching
---------------	----------

SS-3R 20X7 WH - Contactor marker

0807740

<https://www.phoenixcontact.com/us/products/0807740>



Classifications

ECLASS

ECLASS-15.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SS-3R 20X7 WH - Contactor marker

0807740

<https://www.phoenixcontact.com/us/products/0807740>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com