

CRIMPFOX-RC 2,5 - Crimping pliers



1212063

<https://www.phoenixcontact.com/us/products/1212063>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for uninsulated cable lugs, 0.34 ... 2.5 mm², indent crimp

Your advantages

- Unlockable pressure lock
- Lateral conductor entry
- Consistently high crimping quality
- Compact and lightweight design
- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working
- Marked die stations for precise processing of corresponding cross sections
- Crimping pliers for uninsulated cable lugs

Commercial data

Item number	1212063
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3133
GTIN	4046356453844
Weight per piece (including packing)	436.4 g
Weight per piece (excluding packing)	435.3 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-RC 2,5 - Crimping pliers



1212063

<https://www.phoenixcontact.com/us/products/1212063>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Indent crimp
Product property	Unlockable pressure lock
	Lateral conductor entry
	Compact and lightweight design
	Marked die stations

Crimping position 1

Min. cross section	0.34 mm ²
Max. cross section	0.75 mm ²
AWG min	22
AWG max	20

Crimping position 2

Min. cross section	0.75 mm ²
Max. cross section	1.5 mm ²
AWG min	14
AWG max	16

Crimping position 3

Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14

Connection data

Conductor connection

Cross section range, metric	0.34 mm ² ... 2.5 mm ²
Cross section range AWG	22 ... 14

Dimensions

Width	18 mm
Height	59 mm
Length	198 mm

Material specifications

CRIMPFOX-RC 2,5 - Crimping pliers



1212063

<https://www.phoenixcontact.com/us/products/1212063>

Color	black
-------	-------

CRIMPFOX-RC 2,5 - Crimping pliers


1212063

<https://www.phoenixcontact.com/us/products/1212063>



Drawings

Product drawing



CRIMPFOX-RC 2,5 - Crimping pliers

1212063

<https://www.phoenixcontact.com/us/products/1212063>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212063>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-RC 2,5 - Crimping pliers



1212063

<https://www.phoenixcontact.com/us/products/1212063>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-RC 2,5 - Crimping pliers



1212063
<https://www.phoenixcontact.com/us/products/1212063>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com