

CUTFOX-S VDE_DB - Diagonal cutter

1212790

<https://www.phoenixcontact.com/us/products/1212790>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested, type of packaging: with holder for sales display (backcard)

Your advantages

- Inductively hardened blades for long-term stable cutting performance
- VDE-tested cutting tools made from special high-grade tool steel

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212790 |
| Packing unit | 1 pc |
| Minimum order quantity | 6 pc |
| Sales key | BH31 |
| Product key | BH311S |
| GTIN | 4046356994668 |
| Weight per piece (including packing) | 227.9 g |
| Weight per piece (excluding packing) | 227.9 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

CUTFOX-S VDE_DB - Diagonal cutter

1212790

<https://www.phoenixcontact.com/us/products/1212790>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

| | |
|--------------|----------------------|
| Product type | Cutting tool |
| Application | Al + Cu + piano wire |

Dimensions

| | |
|--------|--------|
| Length | 160 mm |
|--------|--------|

Material specifications

| | |
|-------|----------------------|
| Color | multicolored (RAL -) |
|-------|----------------------|

Cable/line

| | |
|-------------------------|------------------|
| External cable diameter | 0.2 mm ... 11 mm |
|-------------------------|------------------|

Standards and regulations

| | |
|-------|----------------------------------|
| Tests | DIN EN 60900 (VDE 0682 PART 201) |
| | DIN ISO 5746 |

CUTFOX-S VDE_DB - Diagonal cutter

1212790

<https://www.phoenixcontact.com/us/products/1212790>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212790>



EAC

Approval ID: RU x-DE.xx08.B.02974



VDE approval of drawings

Approval ID: 40052526

CUTFOX-S VDE_DB - Diagonal cutter

1212790

<https://www.phoenixcontact.com/us/products/1212790>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043711 |
| ECLASS-15.0 | 21043711 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000165 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CUTFOX-S VDE_DB - Diagonal cutter

1212790

<https://www.phoenixcontact.com/us/products/1212790>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com