

# HC-B10-BCSFS-P-BK - Protective cover

1414625

<https://www.phoenixcontact.com/us/products/1414625>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover B10, for single locking latch, protective cover material: PA, height: 18.5 mm, seal: no



## Commercial data

Item number	1414625
Packing unit	1 pc
Sales key	BF66
Product key	AF7AZC
GTIN	4055626030661
Weight per piece (including packing)	26.6 g
Weight per piece (excluding packing)	20.488 g
Customs tariff number	85389099
Country of origin	DE

# HC-B10-BCSFS-P-BK - Protective cover

1414625

<https://www.phoenixcontact.com/us/products/1414625>



## Technical data

### Notes

General	Protective cover for supporting base element with single locking latch
---------	--

### Product properties

Product type	Protective cover
Housing type	Protective cover
Type	B10
Seal present	no

### Dimensions

Dimensional drawing	
Width	46 mm
Height	18.5 mm
Length	76 mm
Diameter	40 mm

### Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	HB
Material, protective cover	PA

### Mechanical properties

Mechanical data	
Locking type	Pin

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

### Mounting

Assembly note	Plastic protective cover for short-term protection
---------------	--

# HC-B10-BCSFS-P-BK - Protective cover


1414625

<https://www.phoenixcontact.com/us/products/1414625>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-B10-BCSFS-P-BK - Protective cover

1414625

<https://www.phoenixcontact.com/us/products/1414625>



## Classifications

### ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

### ETIM

ETIM 8.0	EC002314
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-B10-BCSFS-P-BK - Protective cover

1414625

<https://www.phoenixcontact.com/us/products/1414625>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)