

SACC-AT06-3S-IV - Connector housing



1520762

<https://www.phoenixcontact.com/us/products/1520762>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector housing, 3-position, Crimp contacts

Commercial data

Item number	1520762
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF72
Product key	AF2IEA
GTIN	4063151983765
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	5 g
Country of origin	MX

SACC-AT06-3S-IV - Connector housing



1520762

<https://www.phoenixcontact.com/us/products/1520762>

Technical data

Notes

General	AT06-3S-BLK
General	Use with Size 16 socket contacts

Product properties

Product type	Contact insert
Series	AT06
Number of positions	3
Contact numbering	A, B, C
Shielded	no


Electrical properties

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
Insulation resistance	1000 MΩ (at 25 °C)
Nominal voltage U_N	50 V AC/DC (IEC rating)
Nominal current I_N	13 A (MAX)

Connection data

Connection method	Crimp contacts
-------------------	----------------

Dimensions

Dimensional drawing	
Width	18.4 mm
Height	19 mm
Length	28.6 mm

Material specifications

Seal material Profile gasket	Silicon
Seal material Cable seal	Silicon
Housing material	PA-GF

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Characteristics

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
------------------------------	--

SACC-AT06-3S-IV - Connector housing



1520762

<https://www.phoenixcontact.com/us/products/1520762>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68 (in mated condition)
	IP69K (in mated condition)
Ambient temperature (operation)	-55 °C ... 125 °C


SACC-AT06-3S-IV - Connector housing

1520762

<https://www.phoenixcontact.com/us/products/1520762>


Drawings

Dimensional drawing



AT06-3S top view and side view

Schematic diagram



AT06-3S pin assignment

SACC-AT06-3S-IV - Connector housing



1520762

<https://www.phoenixcontact.com/us/products/1520762>

Classifications

ECLASS

ECLASS-15.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

SACC-AT06-3S-IV - Connector housing



1520762

<https://www.phoenixcontact.com/us/products/1520762>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com