

EMD-SL-PS- 24DC - Power module



2885359

<https://www.phoenixcontact.com/us/products/2885359>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power modules, pluggable, for EMD-SL-..., supply voltage: 20 V DC ... 30 V DC

Your advantages

- Separately adjustable startup and response delays
- Variable supply voltage range
- Adjustable via potentiometer on the front

Commercial data

Item number	2885359
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK663Z
GTIN	4046356049887
Weight per piece (including packing)	24.1 g
Weight per piece (excluding packing)	21 g
Customs tariff number	85043180
Country of origin	AT

EMD-SL-PS- 24DC - Power module

2885359

<https://www.phoenixcontact.com/us/products/2885359>



Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Power module
--------------	--------------

Input data

Input voltage	24 V DC
Input voltage range DC	20 V DC ... 30 V DC

Dimensions

Width	32 mm
Height	35 mm
Depth	16 mm
Horizontal pitch	1.8 Div.

Material specifications

Housing material	Plastic
------------------	---------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

EMD-SL-PS- 24DC - Power module



2885359

<https://www.phoenixcontact.com/us/products/2885359>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

EMD-SL-PS- 24DC - Power module



2885359

<https://www.phoenixcontact.com/us/products/2885359>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com