

# CONFIG+ DEMO - Configuration and diagnostic software



2868046

<https://www.phoenixcontact.com/us/products/2868046>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Config+ Demo version with limited range of functions (unable to save projects). The demo version is available free of charge and does not require a license key. It is part of the AUTOMATIONWORX Software Suite, which you can download under "Downloads".

## Product description

Config+ from Phoenix Contact is the ideal software solution for configuring INTERBUS networks.

The clear user interface allows you to assign addresses using drag & drop and to reliably configure even complex topologies. In addition, the Ethernet devices used can also be mapped and diagnosed. For reliable troubleshooting in INTERBUS networks, the integrated Diag+ diagnostics tool can be used.

## Your advantages

- Reading in and comparing the real and configured topology
- Parameterization of master boards or controller boards, even several boards in one project
- Parameterization of several devices with assistant support (MDC wizard)
- Configuration of INTERBUS and Ethernet networks
- Device parameterization via FDT by means of integratable DTM
- Monitor function for wiring checks
- IP address assignment via BootP server
- Automatic address assignment or via drag & drop

## Commercial data

Item number	2868046
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRDBAB
GTIN	4046356047005
Weight per piece (including packing)	40.05 g
Weight per piece (excluding packing)	40.05 g
Country of origin	DE

# CONFIG+ DEMO - Configuration and diagnostic software



2868046

<https://www.phoenixcontact.com/us/products/2868046>

## Technical data

### Notes

General	Other controller boards available on request
---------	--

### Product properties

Product type	Configuration and diagnostics
Basic functions	Project planning of Ethernet configurations Planning of the address assignment Comparison between real and planned bus configuration Comprehensive diagnostic functions, including optical diagnostics with Diag+ Network diagnostics (functionality of Diag+)

### System properties

Control system	STEP 7 (G4)
Type of software	On-premises
Intended use for the software	Configuration

### License information

Type of license	Single-user license Freeware
-----------------	---------------------------------

### Functionality

Basic functions	Project planning of Ethernet configurations Planning of the address assignment Comparison between real and planned bus configuration Comprehensive diagnostic functions, including optical diagnostics with Diag+ Network diagnostics (functionality of Diag+)
Integrated function	Diagnostics Evaluation Data acquisition Startup Communication Configuration Maintenance Functional safety
Configuration	INTERBUS Ethernet
Diagnostics	INTERBUS Ethernet
Control system	STEP 7 (G4)
Associated hardware	4th generation INTERBUS controller boards, PROFINET controller (Phoenix Contact only)

# CONFIG+ DEMO - Configuration and diagnostic software



2868046

<https://www.phoenixcontact.com/us/products/2868046>

Termination boards supported	2719962 IBS S7 400 DSC/I-T 2719975 IBS S7 300 DSC-T 2730080 IBS PCI SC/RI/I-T 2730187 IBS PCI SC/RI-LK 2725260 IBS PCI SC/I-T 2700318 IBS PCI SC-LK 2862327 FL IL 24 BK-B-PAC 2862314 FL IL 24 BK-PAC 2985974 FL NP PND-4TX IB 2985929 FL NP PND-4TX IB-LK 2736916 FLM BK ETH M12 DI 8 M12-2TX 2703981 IL ETH BK DI8 DO4 2TX-PAC
Supported controllers	Further controller boards on request.
Number of I/O nodes	not relevant

## System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 10 (32-bit/64-bit), as of Build 1511 Windows®11, as of Build 22000.675
Processor	min. 2 GHz, x86 architecture
Hard disk memory	min. 2 GByte
Interfaces	Serial interface, Ethernet, PCI
Supported browsers	Internet Explorer Version 8 or later
Languages supported	German, English, French, Italian, Spanish, Chinese
Screen resolution	SXGA (1280 x 1024)

# CONFIG+ DEMO - Configuration and diagnostic software



2868046

<https://www.phoenixcontact.com/us/products/2868046>

## Classifications

### UNSPSC

UNSPSC 21.0

43233603

# CONFIG+ DEMO - Configuration and diagnostic software



2868046

<https://www.phoenixcontact.com/us/products/2868046>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)