

# USBR 2-11 - Bridge bar

3001356

<https://www.phoenixcontact.com/us/products/3001356>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge bar, number of positions: 2, color: silver-colored



## Commercial data

Item number	3001356
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4046356857284
Weight per piece (including packing)	7.26 g
Weight per piece (excluding packing)	7.2 g
Customs tariff number	85369095
Country of origin	IN

# USBR 2-11 - Bridge bar

3001356

<https://www.phoenixcontact.com/us/products/3001356>



## Technical data

### Product properties

Product type	Bridge bar
Number of positions	2
Potentials	2

### Material specifications

Color	silver-colored
-------	----------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# USBR 2-11 - Bridge bar

3001356

<https://www.phoenixcontact.com/us/products/3001356>



## Classifications

### ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

### ETIM

ETIM 9.0	EC000489
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# USBR 2-11 - Bridge bar

3001356

<https://www.phoenixcontact.com/us/products/3001356>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4da2a354-5bc5-4fb1-b109-ae8347569566

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)