

UM-SE-A60 - Lateral element



2955616
<https://www.phoenixcontact.com/us/products/2955616>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element, tall version, for closing both ends of the base element UM-BEFE, for 60 mm wide U-shaped profile cover

The figure shows a combination of versions UM-SE-1, UM 16,5-1 BE, UM-BE 35-1, UM-BEFE 35-1, UM-SE-A 60-R and UM-A/U 73 CM

Commercial data

Item number	2955616
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDDA
GTIN	4017918085582
Weight per piece (including packing)	12.85 g
Weight per piece (excluding packing)	12.6 g
Customs tariff number	85369010
Country of origin	PL

UM-SE-A60 - Lateral element

2955616

<https://www.phoenixcontact.com/us/products/2955616>



Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM ST SE
Ventilation openings present	no

Material specifications

Color (Side element)	green (RAL 6021)
Material Lateral element	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Mounting

Mounting type	Latching
---------------	----------


UM-SE-A60 - Lateral element

2955616

<https://www.phoenixcontact.com/us/products/2955616>



Drawings




UM-SE-A60 - Lateral element

2955616

<https://www.phoenixcontact.com/us/products/2955616>



Dimensional drawing



UM-SE-A60 - Lateral element

2955616

<https://www.phoenixcontact.com/us/products/2955616>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2955616>



UL Recognized

Approval ID: E240868

UM-SE-A60 - Lateral element



2955616

<https://www.phoenixcontact.com/us/products/2955616>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-SE-A60 - Lateral element

2955616

<https://www.phoenixcontact.com/us/products/2955616>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.101 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com