

AH-ME 115X150X80 - Covering hood

3240267

<https://www.phoenixcontact.com/us/products/3240267>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover, for the contact- and dust-protected encapsulation of the components



Your advantages

- The cover can be securely snapped onto the corresponding E/NS 35-N-APH end brackets and sealed as an option
- Cover profiles provide protection against unauthorized actuation of terminal strips
- This profile has been specially adapted to the shape of the test disconnect terminal blocks
- The AH-ME cover, which is enclosed on all sides, is snapped onto the end brackets and can be sealed as an option

Commercial data

Item number	3240267
Packing unit	5 pc
Minimum order quantity	5 pc
Product key	BE61ZX
GTIN	4055626049571
Weight per piece (including packing)	153.04 g
Weight per piece (excluding packing)	151.5 g
Country of origin	DE

AH-ME 115X150X80 - Covering hood

3240267

<https://www.phoenixcontact.com/us/products/3240267>



Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Dimensional drawing	
Width	150 mm
Height	115 mm
Depth	80 mm
Length	115 mm

Material specifications

Color	transparent
Material	PC
Flammability rating according to UL 94	V0
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

AH-ME 115X150X80 - Covering hood





3240267

<https://www.phoenixcontact.com/us/products/3240267>

Drawings

Dimensional drawing



AH-ME 115X150X80 - Covering hood

3240267

<https://www.phoenixcontact.com/us/products/3240267>



Classifications

ECLASS

ECLASS-13.0	27141190
-------------	----------

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AH-ME 115X150X80 - Covering hood

3240267

<https://www.phoenixcontact.com/us/products/3240267>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com