

# C-SCMI 2,5/6,3X0,8 - Connector

3240059

<https://www.phoenixcontact.com/us/products/3240059>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flat connector, blue, 1.5 - 2.5 mm<sup>2</sup>, 6.3 x 0.8

## Your advantages

- "Easy Entry" for easy and reliable conductor entry
- Halogen-free
- Hard-soldered crimping zone for maximum pull-out forces
- Electrogalvanized

## Commercial data

Item number	3240059
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BH34
Product key	BH3451
GTIN	4046356452779
Weight per piece (including packing)	1.02 g
Weight per piece (excluding packing)	1.02 g
Customs tariff number	85366990
Country of origin	CN

# C-SCMI 2,5/6,3X0,8 - Connector

3240059


<https://www.phoenixcontact.com/us/products/3240059>

## Technical data

### Product properties

Product type	Connector
Product property	Halogen-free
	With "Easy Entry" system
	Brazed
	PA-insulated

### Dimensions

Dimensional drawing	
Width	6.3 mm
Sleeve length	22.5 mm
Length of the insulating material sleeve	11 mm
Maximum stripping length	8 mm
Min. material thickness	0.8 mm
Inner dimensions of the insulating collar	4.5 mm

### Material specifications

Color	blue (RAL 5015)
Material	Brass
Flammability rating according to UL 94	V2
Coating	tin-plated
Insulating material	PA
Components	halogen-free

### Mechanical properties

#### Technical data

Sleeve length	22.5 mm
---------------	---------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
---------------------------------	-------------------

# C-SCMI 2,5/6,3X0,8 - Connector


3240059

<https://www.phoenixcontact.com/us/products/3240059>



## Drawings

Dimensional drawing



# C-SCMI 2,5/6,3X0,8 - Connector



3240059

<https://www.phoenixcontact.com/us/products/3240059>

## Classifications

### ECLASS

ECLASS-13.0	27400204
ECLASS-15.0	27400204

### ETIM

ETIM 9.0	EC001052
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# C-SCMI 2,5/6,3X0,8 - Connector



3240059

<https://www.phoenixcontact.com/us/products/3240059>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)