

C-RC 2,5/M10 DIN - Ring cable lug



3240082

<https://www.phoenixcontact.com/us/products/3240082>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ring cable lug, non-insulated, 1.1 ... 2.5 mm², M10



Your advantages

- The CRIMPFOX-RC... tools from our CRIMPFOX range of crimping pliers are available for optimum crimping
- The hard-soldered press zone enables maximum conductor pull-out values to be achieved
- The ring cable lugs without plastic sleeve are made from high-quality tin-plated electrolytic copper for maximum protection against corrosion

Commercial data

Item number	3240082
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH3422
GTIN	4046356452991
Weight per piece (including packing)	1.82 g
Weight per piece (excluding packing)	1.03 g
Customs tariff number	85369010
Country of origin	CN

C-RC 2,5/M10 DIN - Ring cable lug

3240082

<https://www.phoenixcontact.com/us/products/3240082>




Technical data

Product properties

Product type	Connector
Product property	Design according to DIN 46234
	Brazed
	Tin-plated

Dimensions

Dimensional drawing	
	
Width	18 mm
Sleeve length	28 mm
Length of the insulating material sleeve	5 mm
Maximum stripping length	8 mm
Distance from the center to the insulating material sleeve	12 mm
Min. material thickness	0.8 mm
Inner dimensions of the insulating collar	2.3 mm
Internal dimensions	
Internal diameter	10.5 mm

Material specifications

Color	silver-colored
Material	Copper
Coating	tin-plated

Mechanical properties

Technical data	
Sleeve length	28 mm

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	110 °C

Standards and regulations

Design according to standard	DIN 46234
------------------------------	-----------

C-RC 2,5/M10 DIN - Ring cable lug




3240082

<https://www.phoenixcontact.com/us/products/3240082>

Drawings

Dimensional drawing



C-RC 2,5/M10 DIN - Ring cable lug



3240082

<https://www.phoenixcontact.com/us/products/3240082>

Classifications

ECLASS

ECLASS-13.0	27400204
ECLASS-15.0	27400204

ETIM

ETIM 9.0	EC001052
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

C-RC 2,5/M10 DIN - Ring cable lug



3240082

<https://www.phoenixcontact.com/us/products/3240082>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com