

WT-BASE LS HF 4 BK - Cable binder base



3240707

<https://www.phoenixcontact.com/us/products/3240707>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable binder base, for cable binders up to 4 mm wide, self-adhesive (rubber) and screwable, 4 mm fixing hole, 4-sided cable binder feed-through



Commercial data

Item number	3240707
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE07
Product key	BE713Z
GTIN	4046356703949
Weight per piece (including packing)	0.697 g
Weight per piece (excluding packing)	0.696 g
Customs tariff number	39269097
Country of origin	HR

WT-BASE LS HF 4 BK - Cable binder base



3240707

<https://www.phoenixcontact.com/us/products/3240707>

Technical data

Product properties

Product type	Cable tie
Tensile strength GRP	120 N

Dimensions

Width	19 mm
Height	5 mm
Length	19 mm
Hole diameter	4.1 mm
Diameter mounting hole	4 mm

Internal dimensions

Width_inside	4 mm
--------------	------

Material specifications

Color	black (RAL 9005)
Material	ABS
Flammability rating according to UL 94	HB
Components	free from silicone and halogen

Cable/line

Tensile strength	120 N
------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (assembly)	15 °C ... 40 °C

Mounting

Mounting type	Screw mounting
	adhesive

WT-BASE LS HF 4 BK - Cable binder base



3240707

<https://www.phoenixcontact.com/us/products/3240707>

Classifications

ECLASS

ECLASS-13.0	23159090
ECLASS-15.0	23159090

ETIM

ETIM 9.0	EC011571
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

WT-BASE LS HF 4 BK - Cable binder base



3240707

<https://www.phoenixcontact.com/us/products/3240707>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com