

CARRIER-PMP (108X38) - Marker carriers

0830958

<https://www.phoenixcontact.com/us/products/0830958>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker carriers, black, unmarked, mounting type: screw, rivet, text field height: 38 mm, text field width: 90 mm



Your advantages

- The CARRIER-PMP marker carrier is used in conjunction with insertable UCT-PMP ... labels
- They are used to clearly identify devices and control cabinets
- They can be mounted using screws or screw clamps

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0830958 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG12 |
| Product key | BG261A |
| GTIN | 4046356912310 |
| Weight per piece (including packing) | 27.1 g |
| Weight per piece (excluding packing) | 24.45 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

CARRIER-PMP (108X38) - Marker carriers

0830958

<https://www.phoenixcontact.com/us/products/0830958>



Technical data

Product properties

| Product type | Marker carriers |
|--------------|-----------------|
|--------------|-----------------|

Dimensions

| | |
|--------|----------|
| Width | 109.8 mm |
| Height | 42.4 mm |
| Depth | 20 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | black (RAL 9005) |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Mounting

| Mounting type | screw, rivet |
|---------------|--------------|
|---------------|--------------|

CARRIER-PMP (108X38) - Marker carriers

0830958

<https://www.phoenixcontact.com/us/products/0830958>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002248 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CARRIER-PMP (108X38) - Marker carriers

0830958

<https://www.phoenixcontact.com/us/products/0830958>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com