

SD FLASH 8GB PLCNEXT MEMORY LIC - Program/configuration memory



1151112

<https://www.phoenixcontact.com/us/products/1151112>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for storing the application programs, licenses, and other files in the file system of the PLC, plug-in, 8 GB.

Your advantages

- For storing application programs, the licenses, and other files in the file system of the PLC
- Program and configuration memory

Commercial data

Item number	1151112
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR09
Product key	DRADZA
GTIN	4063151149031
Weight per piece (including packing)	9.5 g
Weight per piece (excluding packing)	9 g
Customs tariff number	85235190
Country of origin	DE

SD FLASH 8GB PLCNEXT MEMORY LIC -

Program/configuration memory



1151112

<https://www.phoenixcontact.com/us/products/1151112>

Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type	Storage medium
Application	Program/configuration memory
Mounting position	vertical

Electrical properties

Maximum power dissipation for nominal condition	0.264 W
Supply	
Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC
Typical current consumption	typ. 80 mA

Material specifications

Housing material	Plastic
------------------	---------

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 85 °C

Mounting

Mounting position	vertical
-------------------	----------

SD FLASH 8GB PLCNEXT MEMORY LIC - Program/configuration memory



1151112

<https://www.phoenixcontact.com/us/products/1151112>

Classifications

ECLASS

ECLASS-13.0	27242212
ECLASS-15.0	27242212

ETIM

ETIM 9.0	EC000192
----------	----------

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

SD FLASH 8GB PLCNEXT MEMORY LIC - Program/configuration memory



1151112

<https://www.phoenixcontact.com/us/products/1151112>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com