

WIREFOX-MP VDE - Stripping tool



1212528

<https://www.phoenixcontact.com/us/products/1212528>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multifunction stripping tool, for removing the jacket from cables with a diameter of 8 to 13 mm, for stripping cables with a cross section of 0.2 to 10 mm², with full-fledged diagonal cutter, VDE 1000 V AC/1500 V DC tested

Your advantages

- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212528 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3161 |
| GTIN | 4046356589567 |
| Weight per piece (including packing) | 247.7 g |
| Weight per piece (excluding packing) | 240.5 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

WIREFOX-MP VDE - Stripping tool

1212528

<https://www.phoenixcontact.com/us/products/1212528>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

| | |
|------------------|--|
| Product type | Stripping tool |
| Application | Standard |
| | Aluminum |
| | Copper |
| | Piano wire |
| Product property | Integrated diagonal cutter with additional sheath area |
| | VDE tested |

Connection data

Conductor connection

| | |
|-----------------------------|--|
| Cross section range, metric | 0.2 mm ² ... 10 mm ² (Stripping range) |
| | Cutting zone |
| Cross section range AWG | 24 ... 8 (Stripping range) |
| | Cutting zone |

Stripping length

100 mm

Dimensions

| | |
|---------------------|--------|
| Length | 190 mm |
| External dimensions | |

External dimensions

Outside diameter

8 mm ... 13 mm

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

Cable/line

| | |
|-------------------------|----------------|
| External cable diameter | 8 mm ... 13 mm |
|-------------------------|----------------|

WIREFOX-MP VDE - Stripping tool

1212528

<https://www.phoenixcontact.com/us/products/1212528>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212528>



EAC

Approval ID: RU x-DE.xx08.B.02974



VDE approval of drawings

Approval ID: 40052526

WIREFOX-MP VDE - Stripping tool

1212528

<https://www.phoenixcontact.com/us/products/1212528>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043705 |
| ECLASS-15.0 | 21043705 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000165 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

WIREFOX-MP VDE - Stripping tool

1212528

<https://www.phoenixcontact.com/us/products/1212528>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com