

# SCX-CLAMP 14X51-127 - Mast clamp

1175556

<https://www.phoenixcontact.com/us/products/1175556>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mast clamps, 2 pcs, with quick mounting connection for installation on masts with a diameter of 51 ... 127 mm



## Your advantages

- For mounting the Smart Ethernet Box
- made from high-quality stainless steel
- For outdoor installation
- Easy operation
- Rugged design

## Commercial data

Item number	1175556
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN08
Product key	DNC3Z1
GTIN	4063151205799
Weight per piece (including packing)	146.3 g
Weight per piece (excluding packing)	140 g
Customs tariff number	73269098
Country of origin	DE

# SCX-CLAMP 14X51-127 - Mast clamp

1175556

<https://www.phoenixcontact.com/us/products/1175556>



## Technical data

### Notes

Note on application

Note on application

Only for industrial use

### Product properties

Product type	Mounting material
Manufacturer	Ideal Tridon
Manufacturer Designation	Surelock 48
Manufacturer product number	48001 0072

### Connection data

Tightening torque	5.9 Nm (Recommended maximum torque for standard applications)
-------------------	---

### Dimensions

Width	14.3 mm
-------	---------

### Material specifications

Material (Strap and clamping part)	Stainless steel 1.4301/AISI 304
Material (Screw)	Stainless steel 1.4303/AISI 305

# SCX-CLAMP 14X51-127 - Mast clamp

1175556

<https://www.phoenixcontact.com/us/products/1175556>



## Classifications

### ECLASS

ECLASS-13.0	23159090
ECLASS-15.0	23159090

### ETIM

ETIM 9.0	EC011571
----------	----------

### UNSPSC

UNSPSC 21.0	31162900
-------------	----------

# SCX-CLAMP 14X51-127 - Mast clamp

1175556

<https://www.phoenixcontact.com/us/products/1175556>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)