

ZBM 6 1-10,10-100-BASF 2165352 - Zack marker sheet




1050826

<https://www.phoenixcontact.com/us/products/1050826>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Zack marker sheet, Sheet, white, labeled, mounting type: latching, for terminal block width: 6.2 mm, Number of individual labels: 100, text field height: 7.5 mm, text field width: 5.6 mm



Commercial data

Item number	1050826
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BG2123
GTIN	4017918255619
Weight per piece (including packing)	17.872 g
Weight per piece (excluding packing)	13.88 g
Country of origin	PL

ZBM 6 1-10,10-100-BASF 2165352 - Zack marker sheet



1050826

<https://www.phoenixcontact.com/us/products/1050826>

Technical data

Product properties

Product type	Labeled terminal marker
Pitch	6.2 mm

Marking

Number of individual labels	100
Number of individual labels per row	10
Number of marker strips	10

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Dimensions

Width	5.60 mm
Height	10.50 mm
Depth	4.30 mm
Pitch	6.2 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

ZBM 6 1-10,10-100-BASF 2165352 - Zack marker sheet



1050826

<https://www.phoenixcontact.com/us/products/1050826>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBM 6 1-10,10-100-BASF 2165352 - Zack marker sheet



1050826
<https://www.phoenixcontact.com/us/products/1050826>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com