

TMP-RIBBON 110 WH 100 - Ink ribbon cartridge



0803376

<https://www.phoenixcontact.com/us/products/0803376>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMT(B)...., US-EML(F)...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., US-PML...., roll length: 60 m, width: 110 mm



Commercial data

Item number	0803376
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4055626042152
Weight per piece (including packing)	243 g
Weight per piece (excluding packing)	196 g
Customs tariff number	96121010
Country of origin	DE

TMP-RIBBON 110 WH 100 - Ink ribbon cartridge



0803376

<https://www.phoenixcontact.com/us/products/0803376>

Technical data

Product properties

Product type	Ink ribbon
--------------	------------

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Width	110 mm
Length of roll	60 m

Material specifications

Color	white (RAL 9010)
Material	Polyester

Environmental and real-life conditions

Ambient conditions

Recommended ambient temperature (storage/transport)	5 °C ... 35 °C
Recommended humidity (storage/transport)	30 % ... 80 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	1 Year

TMP-RIBBON 110 WH 100 - Ink ribbon cartridge



0803376

<https://www.phoenixcontact.com/us/products/0803376>

Classifications

ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

ETIM

ETIM 9.0	EC001694
----------	----------

UNSPSC

UNSPSC 21.0	44103100
-------------	----------

TMP-RIBBON 110 WH 100 - Ink ribbon cartridge



0803376

<https://www.phoenixcontact.com/us/products/0803376>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com