

PDZ/4 - Strain relief

3040575

<https://www.phoenixcontact.com/us/products/3040575>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Strain relief, width: 19.8 mm, height: 28.9 mm, number of positions: 4, color: black



Your advantages

- The conductor can be fixed using Phoenix Contact cable binders
- The strain relief is snapped into the plug center on the spring-cage plugs or spring-cage couplings

Commercial data

Item number	3040575
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE02
Product key	BE214Z
GTIN	4017918832711
Weight per piece (including packing)	0.836 g
Weight per piece (excluding packing)	0.81 g
Customs tariff number	39269097
Country of origin	PL

PDZ/4 - Strain relief

3040575

<https://www.phoenixcontact.com/us/products/3040575>



Technical data

Product properties

Product type	Mounting material
Number of positions	4

Dimensions

Width	19.8 mm
Height	28.9 mm

Material specifications

Color	black (RAL 9005)
Material	PA-GF
Flammability rating according to UL 94	V0

PDZ/4 - Strain relief

3040575

<https://www.phoenixcontact.com/us/products/3040575>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3040575>



EAC

Approval ID: RU C-DE.BL08.B.00644

PDZ/4 - Strain relief

3040575

<https://www.phoenixcontact.com/us/products/3040575>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PDZ/4 - Strain relief

3040575

<https://www.phoenixcontact.com/us/products/3040575>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com