

ZB 6,QR:FORTL.ZAHLEN 81-90 - Zack marker strip



1051029:0081

<https://www.phoenixcontact.com/in/products/1051029:0081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, vertically labeled with the consecutive numbers: 81 ... 90, white, for terminal block width: 6.2 mm, mounting type: latching

Commercial data

Item number	1051029:0081
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2
Product key	BG2122
GTIN	4017918511715
Weight per piece (including packing)	1.545 g
Weight per piece (excluding packing)	1.545 g
Customs tariff number	49119900
Country of origin	IN

ZB 6,QR:FORTL.ZAHLEN 81-90 - Zack marker strip



1051029:0081

<https://www.phoenixcontact.com/in/products/1051029:0081>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	6.2 mm

Marking

Printing	81 ... 90
----------	-----------

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Dimensions

Width	6.15 mm
Height	10.5 mm
Depth	4.20 mm
Pitch	6.2 mm

Text field

Text field width	6.15 mm
Text field height	10.50 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

ZB 6,QR:FORTL.ZAHLEN 81-90 - Zack marker strip



1051029:0081

<https://www.phoenixcontact.com/in/products/1051029:0081>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in