

# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool case, equipped with: cable cutter, diagonal cutter, combination and needle-nose pliers, stripping pliers, stripping tools, crimping pliers, screwdrivers, control cabinet key, sample set, box of ferrules

## Commercial data

Item number	1212428
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4046356514613
Weight per piece (including packing)	6,768 g
Weight per piece (excluding packing)	6,768 g
Customs tariff number	82060000
Country of origin	DE

# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



Set consists of

## SAMPLE-TOOL-CASE - Toolbox

1208319

<https://www.phoenixcontact.com/us/products/1208319>

Toolbox, without instruments, with rubber straps as tool fixtures



---

## CRIMPFOX 10S - Crimping pliers

1212045

<https://www.phoenixcontact.com/us/products/1212045>

Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm<sup>2</sup> ... 10 mm<sup>2</sup>, unlockable pressure lock, lateral entry



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## CRIMPFOX-RCI 6 - Crimping pliers

1212057

<https://www.phoenixcontact.com/us/products/1212057>

Crimping pliers, for insulated cable lugs,  $0.5 \text{ mm}^2 \dots 6.0 \text{ mm}^2$  (red, blue, yellow), oval crimp, symmetrical



---

## CUTFOX 18 - Cable-cutting tool

1212129

<https://www.phoenixcontact.com/us/products/1212129>

**Cable cutter**, angled, for copper and aluminum up to 18 mm diameter (up to  $50 \text{ mm}^2$ )



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## CUTFOX-S VDE - Diagonal cutter

1212207

<https://www.phoenixcontact.com/us/products/1212207>

Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested



---

## UNIFOX-C VDE - Combination pliers

1212202

<https://www.phoenixcontact.com/us/products/1212202>

Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## UNIFOX-P VDE - Needle-nose pliers

1212204

<https://www.phoenixcontact.com/us/products/1212204>

**Needle-nose pliers with blade, notched grip area,  
VDE 1000 V AC/1500 V DC tested**



## WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>

Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## WIREFOX-D 11 - Stripping tool

1212160

<https://www.phoenixcontact.com/us/products/1212160>



Stripping tool, for stripping multicore signal, control and fiberglass wires of Ø 2.5 - 11 mm. Insulation thickness up to 1 mm

## WIREFOX-D 40 - Stripping tool

1212161

<https://www.phoenixcontact.com/us/products/1212161>



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



## SZF 0-0,4X2,5 - Screwdriver

1204504

<https://www.phoenixcontact.com/us/products/1204504>

Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip



## SZF 1-0,6X3,5 - Screwdriver

1204517

<https://www.phoenixcontact.com/us/products/1204517>

Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip



# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



## SZF 2-0,8X4,0 - Screwdriver

1204520

<https://www.phoenixcontact.com/us/products/1204520>

Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.8 x 4.0 x 100 mm, 2-component grip, with non-slip grip



## SZF 3-1,0X5,5 - Screwdriver

1206612

<https://www.phoenixcontact.com/us/products/1206612>

Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## SZS 0,4X2,5 VDE - Screwdriver

1205037

<https://www.phoenixcontact.com/us/products/1205037>

Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip



## SZS 0,5X3,0 VDE - Screwdriver

1207404

<https://www.phoenixcontact.com/us/products/1207404>

Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## SZS 1,0X4,0 VDE - Screwdriver

1205066

<https://www.phoenixcontact.com/us/products/1205066>

Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip



## SZS 1,0X6,5 VDE - Screwdriver

1205079

<https://www.phoenixcontact.com/us/products/1205079>

Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## SZK PH1 VDE - Screwdriver

1205150

<https://www.phoenixcontact.com/us/products/1205150>

Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip



---

## SZK PH2 VDE - Screwdriver

1205163

<https://www.phoenixcontact.com/us/products/1205163>

Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip



# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



## SZK PZ1 VDE - Screwdriver

1206450

<https://www.phoenixcontact.com/us/products/1206450>

Screwdriver, PZ crosshead, VDE insulated, size: PZ 1 x 80 mm, 2-component grip, with non-slip grip



---

## SZK PZ2 VDE - Screwdriver

1206463

<https://www.phoenixcontact.com/us/products/1206463>

Screwdriver, PZ crosshead, VDE insulated, size: PZ 2 x 100 mm, 2-component grip, with non-slip grip



# TOOL-CASE BASIC - Toolbox



1212428

<https://www.phoenixcontact.com/us/products/1212428>

## USS 4 - Control cabinet key

1203149

<https://www.phoenixcontact.com/us/products/1203149>

Control cabinet key, metal, for all common types of control cabinet



---

## SAMPLE-TOOL-CASE-CABLE-SET - Sample set

1208335

<https://www.phoenixcontact.com/us/products/1208335>

Tool sample set



# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



## AI SORTI BOX RD - Assortment box

3202960

<https://www.phoenixcontact.com/us/products/3202960>

Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK



# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type	Tool set
Type of packaging	Case

### Dimensions

Width	475 mm
Height	110 mm
Length	425 mm

### Material specifications

Color	multicolored
-------	--------------

# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



## Classifications

### ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

### ETIM

ETIM 9.0	EC000149
----------	----------

### UNSPSC

UNSPSC 21.0	27113200
-------------	----------

# TOOL-CASE BASIC - Toolbox

1212428

<https://www.phoenixcontact.com/us/products/1212428>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)