

MICROFOX-E ESD - Front cutter

1212485

<https://www.phoenixcontact.com/us/products/1212485>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

ESD electronic front cutter, without chamfer, with opening spring



Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept a different ESD-compliant material. In future, the tools will be supplied with plastic handles in black/turquoise. This does not affect the function or quality of the ESD pliers.

Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Through-connected joint for permanent stability and optimum distribution of force
- Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- Special tool steel for permanent use
- Special conductive plastic handles for slow and controlled dissipation of electrostatic energy

Commercial data

Item number	1212485
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3152
GTIN	4046356527170
Weight per piece (including packing)	103 g
Weight per piece (excluding packing)	96.2 g
Customs tariff number	82032000
Country of origin	DE

MICROFOX-E ESD - Front cutter

1212485

<https://www.phoenixcontact.com/us/products/1212485>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Electronics pliers
Product property	Uniform and smooth opening
	Ergonomically designed handle
	Two-component handle
	Push-through joint
	Mirror-polished and phosphated metal surfaces
	ESD tested

Electrical properties

Fuse	DIN EN 61340-5-1/VDE 0300-5-1, DIN EN 61340-2-3/VDE 0300-2-3
------	--

Dimensions

Width	60 mm
Height	8 mm
Length	125 mm

Material specifications

Color	multicolored
Material	Steel
Coating	phosphatized

MICROFOX-E ESD - Front cutter

1212485

<https://www.phoenixcontact.com/us/products/1212485>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212485>



EAC

Approval ID: RU x-DE.xx08.B.02974

MICROFOX-E ESD - Front cutter

1212485

<https://www.phoenixcontact.com/us/products/1212485>



Classifications

ECLASS

ECLASS-13.0	21043712
ECLASS-15.0	21043712

ETIM

ETIM 9.0	EC002222
----------	----------

UNSPSC

UNSPSC 21.0	22101700
-------------	----------

MICROFOX-E ESD - Front cutter

1212485

<https://www.phoenixcontact.com/us/products/1212485>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com