

PSD-S ME BT 110 - Mounting material

2700156

<https://www.phoenixcontact.com/us/products/2700156>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Foot with integrated tube, 110 mm high, black



Commercial data

Item number	2700156
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL117
GTIN	4046356491471
Weight per piece (including packing)	46.7 g
Weight per piece (excluding packing)	46.7 g
Customs tariff number	39269097
Country of origin	DE

PSD-S ME BT 110 - Mounting material

2700156

<https://www.phoenixcontact.com/us/products/2700156>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type	Assembly element
Product family	PSD-S
Scope of supply	1 x seal
	1 x seal

Dimensions

Dimensional drawing	
Height	110 mm
Diameter	70 mm

Material specifications

Color	black
Material	PA-GF

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66/IP69K (as of item revision 01) UL Type 4 (as of item revision 01) UL Type 4X (as of item revision 01) UL Type 12 (as of item revision 01) UL Type 13 (as of item revision 01)
Ambient temperature (operation)	-30 °C ... 60 °C

Mounting

Mounting type	Tube mounting (Seal enclosed)
	Base mounting
Mounting position	any

PSD-S ME BT 110 - Mounting material





2700156

<https://www.phoenixcontact.com/us/products/2700156>

Drawings

Dimensional drawing



PSD-S ME BT 110 - Mounting material

2700156

<https://www.phoenixcontact.com/us/products/2700156>



Classifications

ECLASS

ECLASS-13.0	27371234
ECLASS-15.0	27371234

ETIM

ETIM 9.0	EC001259
----------	----------

UNSPSC

UNSPSC 21.0	46171600
-------------	----------

PSD-S ME BT 110 - Mounting material

2700156

<https://www.phoenixcontact.com/us/products/2700156>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com