

IV-AW8P - Terminal position assurance

1521032

<https://www.phoenixcontact.com/us/products/1521032>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal position assurance, number of positions: 8, material: PA-GF



Commercial data

Item number	1521032
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF72
Product key	AF2IEC
GTIN	4063151985820
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	1.08 g
Country of origin	MX

IV-AW8P - Terminal position assurance



1521032

<https://www.phoenixcontact.com/us/products/1521032>

Technical data

Notes

General	AW8P
General	Use with AT04-8P housings

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--


Product properties

Product type	Terminal position assurance
Series	AT04
Number of positions	8

Electrical properties

Nominal voltage U_N	50 V AC/DC (IEC rating)
-----------------------	-------------------------

Dimensions

Dimensional drawing	
Width	19.3 mm
Height	7.4 mm
Length	14.8 mm

Material specifications

Housing material	PA-GF
------------------	-------

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-55 °C ... 125 °C

IV-AW8P - Terminal position assurance


1521032

<https://www.phoenixcontact.com/us/products/1521032>



Drawings

Dimensional drawing



AW8P top view and side view

IV-AW8P - Terminal position assurance

1521032

<https://www.phoenixcontact.com/us/products/1521032>



Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

IV-AW8P - Terminal position assurance

1521032

<https://www.phoenixcontact.com/us/products/1521032>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com