

RC-06S1N8B0000 - Contact insert

1594145

<https://www.phoenixcontact.com/us/products/1594145>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 6, contact connection type: Socket, Crimp connection, series: NC, RC, RM, TU, UC, this item is expected to be lead-free from Q1 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1594145
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFU
GTIN	4046356199872
Weight per piece (including packing)	12.12 g
Weight per piece (excluding packing)	5.35 g
Customs tariff number	85389099
Country of origin	DE

RC-06S1N8B0000 - Contact insert



1594145

<https://www.phoenixcontact.com/us/products/1594145>

Technical data

Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	6
Connection profile	6
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
Nominal current I _N	20 A (for max. connection cross section)
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Environmental and real-life conditions

RC-06S1N8B0000 - Contact insert



1594145

<https://www.phoenixcontact.com/us/products/1594145>

Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

RC-06S1N8B0000 - Contact insert


1594145

<https://www.phoenixcontact.com/us/products/1594145>



Drawings

Schematic diagram



Connector pin assignment


RC-06S1N8B0000 - Contact insert



1594145

<https://www.phoenixcontact.com/us/products/1594145>

Schematic diagram



Technical drawings can be found under Downloads

RC-06S1N8B0000 - Contact insert



1594145

<https://www.phoenixcontact.com/us/products/1594145>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-06S1N8B0000 - Contact insert



1594145

<https://www.phoenixcontact.com/us/products/1594145>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1cc7a4fe-b050-406d-b59f-c56b0a97b402

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com