

EMG 10-B2 - Electronics housing



2947750

<https://www.phoenixcontact.com/us/products/2947750>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Custom circuit module, consisting of housing, MKDS 3 connection terminal blocks and PCB



Commercial data

Item number	2947750
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCBA
GTIN	4017918082864
Weight per piece (including packing)	22.53 g
Weight per piece (excluding packing)	22.28 g
Customs tariff number	85369010
Country of origin	DE

EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/us/products/2947750>




Technical data

Product properties

Product type	Stackable housing set
Housing type	Component housing
Housing series	EMG
Product family	EMG
Number of positions	4
Pitch	5 mm

Dimensions

Dimensional drawing	
	
Width	10 mm
Installed height	47.5 mm
Height NS 35/7,5	55 mm
	100 mm
Depth	75 mm
Length	75 mm
Pitch	5 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PC (glass-fiber reinforced)
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EMG 10-B2 - Electronics housing


2947750

<https://www.phoenixcontact.com/us/products/2947750>



Drawings

Dimensional drawing



1 = Top edge of the PCB

B = Housing width


EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/us/products/2947750>



Dimensional drawing



Pitch 5 mm

a = Area for mounting components, 38 mm in the hood

b = Area for mounting components, 45 mm in the housing

EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/us/products/2947750>



Classifications

ECLASS

ECLASS-15.0	27190301
ECLASS-13.0	27190301

ETIM

ETIM 9.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EMG 10-B2 - Electronics housing

2947750

<https://www.phoenixcontact.com/us/products/2947750>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com