

FIP-3/2 SERVICE - Interruption plug

3069920

<https://www.phoenixcontact.com/us/products/3069920>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Interruption plug, nom. voltage: 400 V, nominal current: 20 A, color: red



Commercial data

Item number	3069920
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6113
GTIN	4055626136875
Weight per piece (including packing)	31.26 g
Weight per piece (excluding packing)	28.3 g
Customs tariff number	85366990
Country of origin	PL

FIP-3/2 SERVICE - Interruption plug

3069920

<https://www.phoenixcontact.com/us/products/3069920>



Technical data

Product properties

Product type	Plug
Number of positions	2
Pitch	8.2 mm

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Rated surge voltage	4 kV
Test surge voltage	5 kV

Connection data

Nominal current	20 A
Maximum load current	20 A
Nominal voltage	400 V

Dimensions

Width	16.3 mm
Height	53.4 mm
Pitch	8.2 mm

Material specifications

Color	red (RAL 3001)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data	
Open side panel	Yes

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

FIP-3/2 SERVICE - Interruption plug

3069920

<https://www.phoenixcontact.com/us/products/3069920>



Mounting type

Insertion in base strip

FIP-3/2 SERVICE - Interruption plug


3069920

<https://www.phoenixcontact.com/us/products/3069920>



Drawings

Circuit diagram



FIP-3/2 SERVICE - Interruption plug

3069920

<https://www.phoenixcontact.com/us/products/3069920>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FIP-3/2 SERVICE - Interruption plug

3069920

<https://www.phoenixcontact.com/us/products/3069920>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com