

VISU+ 2 SP IEC 61850 - Visualization software

2404835

<https://www.phoenixcontact.com/us/products/2404835>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Driver license for IEC 61850 MMS Client. Only in conjunction with a valid Visu+ runtime license including driver connection (Visu+ RT-D).

Commercial data

Item number	2404835
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DRDADG
GTIN	4055626457789
Weight per piece (including packing)	102.5 g
Weight per piece (excluding packing)	102.5 g
Country of origin	DE

VISU+ 2 SP IEC 61850 - Visualization software

2404835

<https://www.phoenixcontact.com/us/products/2404835>



Technical data

Product properties

Product type	Visualization
Basic functions	Connection as IEC 61850 MMS client to all IEC 61850 MMS servers.

System properties

Intended use for the software	Visualization
-------------------------------	---------------

License information

Type of license	Driver license
-----------------	----------------

Functionality

Basic functions	Connection as IEC 61850 MMS client to all IEC 61850 MMS servers.
Number of I/O nodes	0

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® XP (SP3) Windows® Vista Business Windows® 7 Professional SP1 (32-Bit/64-Bit) Windows® 7 Ultimate SP1 (32-Bit/64-Bit) Windows® 8 Professional (32-Bit/64-Bit) Windows® 8 Enterprise (32-Bit/64-Bit) Windows® Server 2003 Windows® Server 2008 Windows® Server 2008 R2 Windows® 10 (32-Bit/64-Bit)
Hard disk memory	min. 1 GByte (recommended: 2 GB)
RAM	min. 1 GByte (2 GB for Windows Vista and Windows 7)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Optical drive	DVD-ROM
Screen resolution	1024 x 768 pixel(s) (XGA)

VISU+ 2 SP IEC 61850 - Visualization software

2404835

<https://www.phoenixcontact.com/us/products/2404835>



Classifications

ECLASS

ECLASS-13.0	27242502
ECLASS-15.0	27242502

ETIM

ETIM 9.0	EC001416
----------	----------

UNSPSC

UNSPSC 21.0	43231500
-------------	----------

VISU+ 2 SP IEC 61850 - Visualization software

2404835

<https://www.phoenixcontact.com/us/products/2404835>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com