


# CD COVER 100 - Cover profile

3240289

<https://www.phoenixcontact.com/us/products/3240289>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover for cable duct, gray, width: 100 mm, length: 2000 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240289       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE74          |
| Product key                          | BE7431        |
| GTIN                                 | 4046356470162 |
| Weight per piece (including packing) | 662 g         |
| Weight per piece (excluding packing) | 540 g         |
| Customs tariff number                | 39259020      |
| Country of origin                    | DE            |

# CD COVER 100 - Cover profile

3240289

<https://www.phoenixcontact.com/us/products/3240289>



## Technical data

### Product properties

|              |       |
|--------------|-------|
| Product type | Cover |
|--------------|-------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 100 mm  |
| Height | 2000 mm |
| Depth  | 11 mm   |
| Length | 2000 mm |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color                                  | stone gray (RAL 7030) |
| Material                               | PVC                   |
| Flammability rating according to UL 94 | V0                    |
| Components                             | Lead-free             |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 60 °C |
|---------------------------------|------------------|

# CD COVER 100 - Cover profile

3240289

<https://www.phoenixcontact.com/us/products/3240289>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400776 |
| ECLASS-15.0 | 27400776 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000727 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# CD COVER 100 - Cover profile

3240289

<https://www.phoenixcontact.com/us/products/3240289>



## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)