

KMV - Cable marker



0806644

<https://www.phoenixcontact.com/us/products/0806644>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Stainless steel label, silver-colored, unmarked, cable diameter range: 1 ... 63 mm, mounting type: Assembly with cable ties, Number of individual labels: 1, text field height: 19 mm, text field width: 65 mm

Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

Commercial data

Item number	0806644
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG19
Product key	BG2415
GTIN	4017918138684
Weight per piece (including packing)	3.08 g
Weight per piece (excluding packing)	3.129 g
Customs tariff number	73269098
Country of origin	US

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	1
-----------------------------	---

Dimensions

Width	19.00 mm
Height	89.00 mm
Depth	0.90 mm

Material specifications

RoHS compliant	yes
Color	silver-colored
Base element material	Polyester

Cable/line

External cable diameter	1 mm ... 63 mm
-------------------------	----------------

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

KMV - Cable marker

0806644

<https://www.phoenixcontact.com/us/products/0806644>



Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

KMV - Cable marker



0806644
<https://www.phoenixcontact.com/us/products/0806644>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com