

# THERMOMARK GO ACCU - Battery



0805009

<https://www.phoenixcontact.com/us/products/0805009>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Battery for mobile operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

## Commercial data

Item number	0805009
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG03
Product key	BG122Z
GTIN	4055626269139
Weight per piece (including packing)	117 g
Weight per piece (excluding packing)	116 g
Customs tariff number	85076000
Country of origin	CN

# THERMOMARK GO ACCU - Battery

0805009

<https://www.phoenixcontact.com/us/products/0805009>



## Technical data

### Product properties

Product type	Printing system accessories
Battery-operated voltage	7.40 V

### Electrical properties

Battery	
Battery capacity	2.60 Ah

### Energy storage

Battery capacity	2.6 Ah
Battery technology	Lithium-Ion

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C
Ambient temperature (storage/transport)	23 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Shelf life	1 Year

# THERMOMARK GO ACCU - Battery

0805009

<https://www.phoenixcontact.com/us/products/0805009>



## Classifications

### ECLASS

ECLASS-13.0	21052902
ECLASS-15.0	21052902

### ETIM

ETIM 9.0	EC001199
----------	----------

### UNSPSC

UNSPSC 21.0	26111700
-------------	----------

# THERMOMARK GO ACCU - Battery



0805009

<https://www.phoenixcontact.com/us/products/0805009>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)