

PATG 0/23 - Conductor marker carrier



0828046

<https://www.phoenixcontact.com/us/products/0828046>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, transparent, unmarked, cable diameter range: 0.6 ... 1.2 mm, mounting type: slide-on, text field height: 4 mm, text field width: 23 mm

Your advantages

- The corresponding UC-WMT ..., US-WMT ..., and EMT ... insert labels are used for marking

Commercial data

Item number	0828046
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Sales key	BG12
Product key	BG221A
GTIN	4046356467018
Weight per piece (including packing)	0.229 g
Weight per piece (excluding packing)	0.2 g
Customs tariff number	39269097
Country of origin	DE

0828046

<https://www.phoenixcontact.com/us/products/0828046>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	23 mm
Height	4.6 mm
Depth	5.25 mm

Material specifications

RoHS compliant	yes
Color	transparent
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Cable/line

External cable diameter	0.6 mm ... 1.2 mm
-------------------------	-------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	slide-on
---------------	----------

PATG 0/23 - Conductor marker carrier



0828046

<https://www.phoenixcontact.com/us/products/0828046>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PATG 0/23 - Conductor marker carrier



0828046
<https://www.phoenixcontact.com/us/products/0828046>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.001 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com