

EMLP 32 (38X14) SR CUS - Plastic label with drill hole



0824373

<https://www.phoenixcontact.com/us/products/0824373>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label with drill hole, can be ordered: by card, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 6



Your advantages

- High-quality appearance
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers in accordance with your requirements
- High level of resistance to chemical and mechanical influences
- For marking components, devices, and buttons

Commercial data

Item number	0824373
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8141
GTIN	4046356352499
Weight per piece (including packing)	21.69 g
Weight per piece (excluding packing)	21.69 g
Country of origin	PL

EMLP 32 (38X14) SR CUS - Plastic label with drill hole



0824373

<https://www.phoenixcontact.com/us/products/0824373>

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	6
Number of individual labels per row	2

Dimensions

Width	38 mm
Length	50 mm

Material specifications

Adhesive strength	50 µm
Adhesive	Acrylic
Color	silver
Material	TRANSPLY-ABS
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Ambient temperature (storage/transport)	4 °C ... 38 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

EMLP 32 (38X14) SR CUS - Plastic label with drill hole



0824373

<https://www.phoenixcontact.com/us/products/0824373>

Classifications

ECLASS

ECLASS-13.0	27281103
-------------	----------

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMLP 32 (38X14) SR CUS - Plastic label with drill hole



0824373

<https://www.phoenixcontact.com/us/products/0824373>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com