

GPK/SK296X200X0.8 GN/WH - Engraving plate



0826836

<https://www.phoenixcontact.com/us/products/0826836>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device marking

Commercial data

Item number	0826836
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG2415
GTIN	4046356362443
Weight per piece (including packing)	65.116 g
Weight per piece (excluding packing)	57.85 g
Country of origin	DE

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Dimensions

Width	296.00 mm
Height	200.00 mm
Depth	0.93 mm
Length	200 mm

Material specifications

Adhesive strength	50 µm
Adhesive	Acrylic
Color	multicolored (RAL -)
	green (RAL 6021)
	white (RAL 9010)
Material	TRANSPLY-ABS

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
---------------	-------------------------------------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	12 months

Mounting

Mounting type	adhesive
---------------	----------

GPK/SK296X200X0.8 GN/WH - Engraving plate



0826836

<https://www.phoenixcontact.com/us/products/0826836>

Classifications

ECLASS

ECLASS-13.0	27281103
-------------	----------

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

GPK/SK296X200X0.8 GN/WH - Engraving plate



0826836
<https://www.phoenixcontact.com/us/products/0826836>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com