

CK1,6-ER-2,50BU OIC AG - Crimp contact



1004366

<https://www.phoenixcontact.com/us/products/1004366>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-12, Socket, rolled, contact diameter: 1.6 mm, connection cross section: 1.5 mm² ... 2.5 mm², AWG 16...14 , contact material: Cu alloy

Commercial data

Item number	1004366
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	AF7AIB
GTIN	4055626472560
Weight per piece (including packing)	0.361 g
Weight per piece (excluding packing)	0.3 g
Customs tariff number	85366990
Country of origin	TR

CK1,6-ER-2,50BU OIC AG - Crimp contact



1004366

<https://www.phoenixcontact.com/us/products/1004366>

Technical data

Notes

General	This product replaces 1884115 CK1,6-ER-1,50BU AG
---------	--

Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
	HC-M-08-MBIT
Contact material type	rolled


Connection data

Connection technology	
Contact connection type	Socket
Connection method	Crimp connection
Conductor connection	
Stripping length	4 mm
Connection cross section	1.5 mm² ... 2.5 mm²
Connection cross section AWG	16 ... 14

Material specifications

Material Contact	Cu alloy (nickel-plated)
Material Contact surface	Ag

Dimensions

Dimensional drawing	
Length [l]	21 mm
Diameter (Contact diameter)	1.6 mm

Mechanical properties

CK1,6-ER-2,50BU OIC AG - Crimp contact



1004366

<https://www.phoenixcontact.com/us/products/1004366>

Mechanical data

Insertion/withdrawal cycles	≥ 50
-----------------------------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK1,6-ER-2,50BU OIC AG - Crimp contact


1004366

<https://www.phoenixcontact.com/us/products/1004366>



Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ER-2,50BU OIC AG - Crimp contact



1004366

<https://www.phoenixcontact.com/us/products/1004366>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ER-2,50BU OIC AG - Crimp contact



1004366

<https://www.phoenixcontact.com/us/products/1004366>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com