

NS 35/15 AL UNPERF 1000MM - DIN rail, unperforated



1207663
<https://www.phoenixcontact.com/us/products/1207663>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver-colored

Commercial data

Item number	1207663
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	BH84
Product key	BH8422
GTIN	4046356366618
Weight per piece (including packing)	337.422 g
Weight per piece (excluding packing)	337.422 g
Customs tariff number	76042990
Country of origin	AT

NS 35/15 AL UNPERF 1000MM - DIN rail,
unperforated



1207663

<https://www.phoenixcontact.com/us/products/1207663>

Technical data

Product properties

Product type	DIN rail
--------------	----------

Dimensions

Dimensional drawing	
Width	35 mm
Hole width	0 mm
Height	15 mm
Hole height	0 mm
Length	1000 mm
Drill hole spacing	0 mm

Material specifications

Color	silver-colored
Material	Aluminum
Coating	uncoated

Standards and regulations

Tests	similar to EN 60715
-------	---------------------


NS 35/15 AL UNPERF 1000MM - DIN rail, unperforated



1207663

<https://www.phoenixcontact.com/us/products/1207663>

Drawings



NS 35/15 AL UNPERF 1000MM - DIN rail, unperforated



1207663

<https://www.phoenixcontact.com/us/products/1207663>

Classifications

ECLASS

ECLASS-13.0	27400602
ECLASS-15.0	27400602

ETIM

ETIM 9.0	EC001285
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

NS 35/15 AL UNPERF 1000MM - DIN rail, unperforated



1207663
<https://www.phoenixcontact.com/us/products/1207663>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com