

SHN 5.5 - Tool

1209855

<https://www.phoenixcontact.com/us/products/1209855>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Socket wrench, wrench size 5.5 mm



Your advantages

- Ergonomically designed two-component handles for fatigue-proof and non-slip use

Commercial data

Item number	1209855
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH314C
GTIN	4046356178747
Weight per piece (including packing)	73.19 g
Weight per piece (excluding packing)	73.19 g
Customs tariff number	82054000
Country of origin	CZ

SHN 5.5 - Tool

1209855

<https://www.phoenixcontact.com/us/products/1209855>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration


Product properties

Product type	Socket wrench
Type	Hexagonal
Product property	Kraftform handle
	Two-component handle
	Hexagonal non-slip grip
	Hexagonal screw head

Connection data

Output	External hexagonal
--------	--------------------

Dimensions

Dimensional drawing	
	 A technical line drawing of the wrench. It shows a hexagonal socket at the bottom with a handle above it. Dimension 'a' is the height of the handle from the bottom of the socket. Dimension 'b' is the distance from the bottom of the handle to the top of the hexagonal grip. Dimension 'c' is the distance from the top of the handle to the top of the hexagonal head. Dimension 'd' is the total length of the wrench from the bottom of the handle to the end of the hexagonal head.
Width	33 mm
Blade height	70 mm
Length	185 mm
Diameter	33 mm
Wrench size	5.5 mm
Wrench size for mounting	5.5 mm

Material specifications

Color	multicolored
Material	alloyed tool steel

SHN 5.5 - Tool


1209855

<https://www.phoenixcontact.com/us/products/1209855>



Drawings

Dimensional drawing



SHN 5.5 - Tool

1209855

<https://www.phoenixcontact.com/us/products/1209855>



Classifications

ECLASS

ECLASS-13.0	21040206
ECLASS-15.0	21040206

ETIM

ETIM 9.0	EC000174
----------	----------

UNSPSC

UNSPSC 21.0	27111700
-------------	----------

SHN 5.5 - Tool

1209855

<https://www.phoenixcontact.com/us/products/1209855>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com