

CF 500/COV - Covering hood



1212250

<https://www.phoenixcontact.com/us/products/1212250>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hood for CF 500 automatic crimping device, for ferrules: 10 mm² ... 50 mm² (AI 25, AI 50), TWIN ferrules: 6 mm² ... 16 mm² (AI-TWIN 16), uninsulated cable lugs: 16 mm² (RC 16), turned contacts: 6 mm² ... 10 mm² (TC HC 10)

Commercial data

Item number	1212250
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356450126
Weight per piece (including packing)	41.9 g
Weight per piece (excluding packing)	42.8 g
Customs tariff number	84799070
Country of origin	DE

CF 500/COV - Covering hood

1212250

<https://www.phoenixcontact.com/us/products/1212250>



Technical data

Product properties

Product type	Cover
--------------	-------

Connection data

Conductor cross-section flexible	0 mm² ... 0 mm²
----------------------------------	-----------------

Dimensions

Width	22.5 mm
Height	70 mm
Length	105 mm

Material specifications

Color	transparent
Material (Protective cap)	Plastic
Material (Screw connection)	Metal
Material (Screw)	Steel, galvanized

CF 500/COV - Covering hood

1212250

<https://www.phoenixcontact.com/us/products/1212250>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212250>



EAC

Approval ID: RU C-DE.AI30.B.01549

CF 500/COV - Covering hood



1212250

<https://www.phoenixcontact.com/us/products/1212250>

Classifications

ECLASS

ECLASS-13.0	17130192
ECLASS-15.0	17130192

ETIM

ETIM 9.0	EC002778
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 500/COV - Covering hood



1212250

<https://www.phoenixcontact.com/us/products/1212250>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com