

# MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/us/products/1212489>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

## Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Through-connected joint for permanent stability and optimum distribution of force
- Mirror-polished and oiled metal surfaces, which provide maximum rust protection
- Special tool steel for permanent use
- For a variety of applications

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212489       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3151        |
| GTIN                                 | 4046356527200 |
| Weight per piece (including packing) | 88.6 g        |
| Weight per piece (excluding packing) | 84.6 g        |
| Customs tariff number                | 82032000      |
| Country of origin                    | DE            |

# MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/us/products/1212489>



## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |   |
|------------------|---|
| Product type     | Electronics pliers                      |
| Product property | Push-through joint                      |
|                  | Mirror-polished and oiled metal surface |
|                  | Ergonomic two-component handle          |
|                  | Sensitive opening spring                |

### Dimensions

|        |        |
|--------|--------|
| Length | 115 mm |
|--------|--------|

# MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/us/products/1212489>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212489>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/us/products/1212489>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043711 |
| ECLASS-15.0 | 21043711 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000165 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/us/products/1212489>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)